

			Farben (klassisches A-D Farbsystem)														
novo.lign A			BL3	A1	A2	A3	A3,5	A4	B2	B3	B4	C2	C3	D2	D3	D4	
Verblendschalen anterior OK			REF	BL3	A10	A20	A30	A35	A40	B20	B30	B40	C20	C30	D20	D30	D40
C43	6er Set (13, 12, 11, 21, 22, 23)	VOC43	----	S													
C43	4er Set (12, 11, 21, 22)	VOC43	----	4													
C43	2er Set (13, 23)	VOC43	----	3													
A44	6er Set (13, 12, 11, 21, 22, 23)	VOA44	----	S													
A44	4er Set (12, 11, 21, 22)	VOA44	----	4													
A44	2er Set (13, 23)	VOA44	----	3													
I45	6er Set (13, 12, 11, 21, 22, 23)	VOI45	----	S													
I45	4er Set (12, 11, 21, 22)	VOI45	----	4													
I45	2er Set (13, 23)	VOI45	----	3													
S46	6er Set (13, 12, 11, 21, 22, 23)	VOS46	----	S													
S46	4er Set (12, 11, 21, 22)	VOS46	----	4													
S46	2er Set (13, 23)	VOS46	----	3													
I47	6er Set (13, 12, 11, 21, 22, 23)	VOI47	----	S													
I47	4er Set (12, 11, 21, 22)	VOI47	----	4													
I47	2er Set (13, 23)	VOI47	----	3													
D48	6er Set (13, 12, 11, 21, 22, 23)	VOD48	----	S													
D48	4er Set (12, 11, 21, 22)	VOD48	----	4													
D48	2er Set (13, 23)	VOD48	----	3													
M48	6er Set (13, 12, 11, 21, 22, 23)	VOM48	----	S													
M48	4er Set (12, 11, 21, 22)	VOM48	----	4													
M48	2er Set (13, 23)	VOM48	----	3													
D49	6er Set (13, 12, 11, 21, 22, 23)	VOD49	----	S													
D49	4er Set (12, 11, 21, 22)	VOD49	----	4													
D49	2er Set (13, 23)	VOD49	----	3													
B51	6er Set (13, 12, 11, 21, 22, 23)	VOB51	----	S													
B51	4er Set (12, 11, 21, 22)	VOB51	----	4													
B51	2er Set (13, 23)	VOB51	----	3													
K53	6er Set (13, 12, 11, 21, 22, 23)	VOK53	----	S													
K53	4er Set (12, 11, 21, 22)	VOK53	----	4													
K53	2er Set (13, 23)	VOK53	----	3													

Verblendschalen anterior UK

T35	6er Set (43, 42, 41, 31, 32, 33)	VUT35	----	S													
T35	4er Set (42, 41, 31, 32)	VUT35	----	4													
T35	2er Set (43, 33)	VUT35	----	3													
D38	6er Set (43, 42, 41, 31, 32, 33)	VUD38	----	S													
D38	4er Set (42, 41, 31, 32)	VUD38	----	4													
D38	2er Set (43, 33)	VUD38	----	3													
D41	6er Set (43, 42, 41, 31, 32, 33)	VUD41	----	S													
D41	4er Set (42, 41, 31, 32)	VUD41	----	4													
D41	2er Set (43, 33)	VUD41	----	3													

			Farben (klassisches A-D Farbsystem)														
novo.lign P, multifunktional			BL3	A1	A2	A3	A3,5	A4	B2	B3	B4	C2	C3	D2	D3	D4	
Verblendschalen posterior G 3			REF	BL3	A10	A20	A30	A35	A40	B20	B30	B40	C20	C30	D20	D30	D40
1G3	1. Quadrant, (14, 15, 16, 17)	VO1G3	----														
2G3	2. Quadrant, (24, 25, 26, 27)	VO2G3	----														
3G3	3. Quadrant, (34, 35, 36, 37)	VU3G3	----														
4G3	4. Quadrant, (44, 45, 46, 47)	VU4G3	----														

Verblendschalen posterior G 4			REF	BL3	A10	A20	A30	A35	A40	B20	B30	B40	C20	C30	D20	D30	D40
1G4	1. Quadrant, (14, 15, 16, 17)	VO1G4	----														
2G4	2. Quadrant, (24, 25, 26, 27)	VO2G4	----														
3G4	3. Quadrant, (34, 35, 36, 37)	VU3G4	----														
4G4	4. Quadrant, (44, 45, 46, 47)	VU4G4	----														

novo.lign P, Kronen- und Brückentechnik			BL3	A1	A2	A3	A3,5	A4	B2	B3	B4	C2	C3	D2	D3	D4	
Verblendschalen posterior W 3			REF	BL3	A10	A20	A30	A35	A40	B20	B30	B40	C20	C30	D20	D30	D40
1W3	1. Quadrant, (14, 15, 16, 17)	VO1W3	----														
2W3	2. Quadrant, (24, 25, 26, 27)	VO2W3	----														
3W3	3. Quadrant, (34, 35, 36, 37)	VU3W3	----														
4W3	4. Quadrant, (44, 45, 46, 47)	VU4W3	----														

Bitte Bestellmenge eintragen.

		BL3	A1	A2	A3	A3,5	A4	B2	B3	B4	C2	C3	D2	D3	D4
combo.lign	REF	BL3	A10	A20	A30	A35	A40	B20	B30	B40	C20	C30	D20	D30	D40
Befestigungs-Composite, 8 g	CO2X4 ---														
Mischkanülen, 10 St.	COM KG21 0														

combo.lign zahnfleischfarben	VPE	REF	Menge
Composite dualhärtend	8 g	CO2X4GUM	

visio.link	VPE	REF	Menge
PMMA und Composite Primer	10 ml	VLP MMA1 0	

visio.sil	VPE	REF	Menge
visio.sil Transparent	50 ml	540 0120 0	
Mischkanülen visio.sil	12 St.	320 0045 7	
visio.sil fix feinzeichnend	50 ml	540 0130 0	
Mischkanülen visio.sil	12 St.	320 0045 1	

combo.lign Opaquer	VPE	REF	Menge
light für A1 / A2 / A3 / B2	4 g	CO1X40PL	
medium für A3,5 / B3 / D3	4 g	CO1X40PM	
intensiv für A4 / C3	4 g	CO1X40PI	
GUM	4 g	CO1X40PG	
Katalyst für alle Farben	4 g	CO1X4Kat	
alle 4 Farben + 2 x Kat	6 x 4 g	OLIGNSET1	

beauty setup Wachs	VPE	REF	Menge
beauty setup hell	25 g	430 0030 0	
beauty setup dunkel	25 g	430 0031 0	

Dispenser	VPE	REF	Menge
Dispenser 5 ml 1:1	1 St.	320 0044 1	

visio.lign Toolkit	VPE	REF	Menge
Composite Ausarbeitungsset	1 St.	VLTOOLKIT	

crea.lign Zubehör	VPE	REF	Menge
Einhandgriff crea.lign Spritze	1 St.	320 0044 2	
Applikationskanülen	10 St.	320 0094 0	
crea.lign Spritzenhalter	1 St.	320 0044 3	

crea.lign	VPE	REF	Menge
crea.lign Dentin BL3	5 g	CLFNDBL3	
crea.lign Dentin A1	5 g	CLFNDA10	
crea.lign Dentin A2	5 g	CLFNDA20	
crea.lign Dentin A3	5 g	CLFNDA30	
crea.lign Dentin A3,5	5 g	CLFNDA35	
crea.lign Dentin A4	5 g	CLFNDA40	
crea.lign Dentin B2	5 g	CLFNDB20	
crea.lign Dentin B3	5 g	CLFNDB30	
crea.lign Dentin B4	5 g	CLFNDB40	
crea.lign Dentin C2	5 g	CLFNDC20	
crea.lign Dentin C3	5 g	CLFNDC30	
crea.lign Dentin D2	5 g	CLFNDD20	
crea.lign Dentin D3	5 g	CLFNDD30	
crea.lign Dentin D4	5 g	CLFNDD40	

crea.lign Incisal E2	5 g	CLFN00E2	
crea.lign Incisal E3	5 g	CLFN00E3	
crea.lign Incisal opal	5 g	CLFN00I1	
crea.lign Incisal blue	5 g	CLFN00I2	
crea.lign Incisal rose	5 g	CLFN00I3	
crea.lign Incisal universal	5 g	CLFN00I4	

crea.lign GUM light	5 g	CLFN00G1	
crea.lign GUM rosa	5 g	CLFN00G2	
crea.lign GUM pink	5 g	CLFN00G3	

crea.lign Modifier beige	5 g	CLFN00M1	
crea.lign Modifier oliv	5 g	CLFN00M2	
crea.lign Modifier caramel	5 g	CLFN00M3	
crea.lign Modifier lila	5 g	CLFN00M4	

crea.lign Stain orange	1,4 g	CLFN00S1	
crea.lign Stain brown	1,4 g	CLFN00S2	
crea.lign Modelling Liquid	10 ml	CLFMOD10	

crea.lign Starterkit													REF		Menge	
10 Spritzen a 5 g (nach Wahl)													CLIGNSETN			
DBL3	DA1	DA2	DA3	DA3,5	DA4	DB2	DB3	DC3	DD3	E2	E3	I opal	I blue	G light	G rosa	G pink

Bitte 10 Farben kennzeichnen mit X

visio.lign Verblendsystem Starterkit 2	REF	Farbe
10 x novo.lign A, 8 x novo.lign P, 1 x combo.lign, 1 x Mischkanülen, 1 x visio.link, 21-tlg., Farbe nach Wahl	VLIGNSET2	

visio.lign Verblendsystem Starterkit 3	REF	Farbe
wie VLIGNSET2, 2 x crea.lign, 2x Opaquer combo.lign, 12 (statt 10) x novo.lign A, 27-tlg., Farbe nach Wahl	VLIGNSET3	

Absender (Stempel):

Kunden-Nr.

Datum, Unterschrift

			Farben (klassisches A-D Farbsystem)													
			A1	A2	A3	A3,5	A4	B2	B3	B4	C2	C3	D2	D3	D4	
neo.lign A	REF		A10	A20	A30	A35	A40	B20	B30	B40	C20	C30	D20	D30	D40	
Frontzähne anterior OK																
C43 6er Set (13, 12, 11, 21, 22, 23)	TOC43	----	S													
A44 6er Set (13, 12, 11, 21, 22, 23)	TOA44	----	S													
I45 6er Set (13, 12, 11, 21, 22, 23)	TOI45	----	S													
S46 6er Set (13, 12, 11, 21, 22, 23)	TOS46	----	S													
I47 6er Set (13, 12, 11, 21, 22, 23)	TOI47	----	S													
D48 6er Set (13, 12, 11, 21, 22, 23)	TOD48	----	S													
M48 6er Set (13, 12, 11, 21, 22, 23)	TOM48	----	S													
D49 6er Set (13, 12, 11, 21, 22, 23)	TOD49	----	S													
B51 6er Set (13, 12, 11, 21, 22, 23)	TOB51	----	S													
Frontzähne anterior UK																
T35 6er Set (43, 42, 41, 31, 32, 33)	TUT35	----	S													
D38 6er Set (43, 42, 41, 31, 32, 33)	TUD38	----	S													
D41 6er Set (43, 42, 41, 31, 32, 33)	TUD41	----	S													

			Farben (klassisches A-D Farbsystem)													
			A1	A2	A3	A3,5	A4	B2	B3	B4	C2	C3	D2	D3	D4	
neo.lign P, multifunktionell	REF		A10	A20	A30	A35	A40	B20	B30	B40	C20	C30	D20	D30	D40	
Seitenzähne posterior Größe 2																
1G2 1. Quadrant, (14, 15, 16, 17)	T01G2	----														
2G2 2. Quadrant, (24, 25, 26, 27)	T02G2	----														
3G2 3. Quadrant, (34, 35, 36, 37)	TU3G2	----														
4G2 4. Quadrant, (44, 45, 46, 47)	TU4G2	----														
Seitenzähne posterior Größe 3																
1G3 1. Quadrant, (14, 15, 16, 17)	T01G3	----														
2G3 2. Quadrant, (24, 25, 26, 27)	T02G3	----														
3G3 3. Quadrant, (34, 35, 36, 37)	TU3G3	----														
4G3 4. Quadrant, (44, 45, 46, 47)	TU4G3	----														
Seitenzähne posterior Größe 4																
1G4 1. Quadrant, (14, 15, 16, 17)	T01G4	----														
2G4 2. Quadrant, (24, 25, 26, 27)	T02G4	----														
3G4 3. Quadrant, (34, 35, 36, 37)	TU3G4	----														
4G4 4. Quadrant, (44, 45, 46, 47)	TU4G4	----														

Lebende Formenkarte neo.lign	REF	Farbe
24-tlg. (12 x neo.lign A, 12 x neo.lign P), Farbe nach Wahl	VLIGNPRV	

neo.lign Upgrade Kit													REF	Menge		
24-tlg. (12 x neo.lign A, 12 x neo.lign P)													NLUPSET2			
DBL3	DA1	DA2	DA3	DA3,5	DA4	DB2	DB3	DC3	DD3	I rose	I opal	I blue	I univ.	G light	G rosa	G pink

Bitte Bestellmenge eintragen.

Absender (Stempel):

Kunden-Nr.

Datum, Unterschrift